

TechSoft Hegner Fretsaw Stands



MM-FRETSAW19

This unit includes the stand, a Multicut 1-EDU fretsaw, an auto-switching extraction unit and a footswitch. Auto-switching ensures the extraction runs whenever material is being cut. Also available without the saw for schools needing a convenient solution to bring existing machinery up to current H&S regulations, or for those who wish to purchase one of the other Hegner models.

Specification	
Table Height:	840mm (adjustable)
Dimensions:	750(W) x 750(D) x 840(H)mm
Power Requirements:	240V 13A, Lockable rotary isolator
Warranty:	UK Mainland: 1 Year Return to Base Elsewhere: 1 Year Return & Collect

Prices £*		*See Pricing Information on page 2
MM-FRETSAW19	TechSoft Fretsaw Workstation 750 x 750 x 840mm (adjustable), c/w 1 Hegner Multicut EDU-1 saw, auto-switching Mobile Extractor and Footswitch	
MM-EXTRACT104P2	TechSoft Fretsaw Workstation 750 x 750 x 840mm. Excluding Fretsaw but complete with auto-switching Mobile Extractor and Footswitch.	

Other Fretsaw Stands

These provide a stable base for safe working and a flexible solution for workshop layouts.




SF-STAND5



SF-STAND7

Prices £*		*See Pricing Information on page 2
SF-STAND5	Machine Bench, 700 x 600mm, adjustable height, MPX Top	
SF-STAND7	Machine Bench, 700 x 600mm, adjustable height, MPX Top with underbench cupboard containing shelf	

Double Hegner Fretsaw Workstation



MM-FRETSAW3

This workstation provides two Multicut 1-EDU fretsaws on a robust unit for permanent siting. Each saw has its own footswitch and is connected to the on-board extraction unit.

Specification	
Table Height:	805mm
Dimensions:	1500(W) x 800(D) x 805(H)mm
Power Requirements:	240V 13A, Lockable rotary isolator
Warranty:	UK Mainland: 1 Year Return to Base Elsewhere: 1 Year Return & Collect

Prices £*		*See Pricing Information on page 2
MM-FRETSAW3	Double Hegner Fretsaw Workstation (Includes 2 Multicut 1 - EDU fretsaws, auto extraction system & 2 footswitches)	
MMP-EXT-FSCART	Replacement Filter Cartridge for Extractor Used in MM-FRETSAW3	